

**HDC-CR24-7S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The frames of the modular ConCept system allow ConCept modules to be attached. These frames are designed for sizes 3, 4, 6 and 8. Thus they can be fitted into corresponding enclosures of these sizes.

The fitting capacity of the frames ranges from 2 modules up to 7 modules. This allows the user to put together a custom connector assembly. .

The basic version consists of sturdy, one-piece modules frames available to the user in either polycarbonate or die-cast zinc

Frames are only compatible with each other when they are made of the same material and identical size.

**General ordering data**

Version	Heavy-duty connectors, HDC insert, ConCept frame
Order No.	<a href="#">1682240000</a>
Type	HDC-CR24-7S
GTIN (EAN)	4008 190473976
Qty.	5 pc(s).

Creation date March 9, 2023 11:26:29 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**HDC-CR24-7S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	111 mm	Depth (inches)	4.37 inch
Height	35 mm	Height (inches)	1.378 inch
Width	34 mm	Width (inches)	1.339 inch
Net weight	59.2 g		

**Temperatures**

Operating temperature, min.	-40 °C	Operating temperature, max.	125 °C
-----------------------------	--------	-----------------------------	--------

**ConCept Pneumatic module**

Colour	black
--------	-------

**Dimensions**

Height of plug	35 mm	Total length base	111 mm
Width	34 mm		

**General data**

BG	8	Free from halogens	false
Low smoke acc. DIN EN 45545-2	Yes	Material	Polyamide, glass fibre-reinforced
Series	ConCept frame	Size	8
Type	Pin		

**Connection data PE**

Connection type PE	Screw connection	Tightening torque, max. PE connection	1.5 Nm
Tightening torque, min. PE connection	1.2 Nm		

**Version**

BG	8	Material	Polyamide, glass fibre-reinforced
Size	8		

**Classifications**

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ECLASS 9.0	27-44-02-06
ECLASS 9.1	27-44-02-06	ECLASS 10.0	27-44-02-06
ECLASS 11.0	27-44-02-06	ECLASS 12.0	27-44-02-92

**Approvals**

Approvals



ROHS

Conform

**Data sheet**

**HDC-CR24-7S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
  
[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Downloads**

---

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>

---