

SM 27/12.5 SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | SwitchMark, Device markers, 12.5 x 27 mm, SwitchMark holder, To customer specification |
| Order No. | 1699850000 |
| Type | SM 27/12.5 SDR |
| GTIN (EAN) | 4008190892296 |
| Qty. | 16 Stück |
| compatible printer | 2715590000 2438520000 2438510000 |

SM 27/12.5 SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 1 mm | Depth (inches) | 0.039 inch |
| Height | 12.5 mm | Height (inches) | 0.492 inch |
| Width | 27 mm | Width (inches) | 1.063 inch |
| Net weight | 0.81 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|-------------------|-----------------------------------|---|
| Application/manufacture | SwitchMark holder | Colour | To customer specification |
| Colour of printing | black | Halogen | No |
| Material | Polyamide 66 | Number of markers per combination | 1 MultiCard = Device markers |
| Operating temperature range | -40...100 °C | Operating temperature range, max. | 100 °C |
| Operating temperature range, min. | -40 °C | Printed characters | Based on customer requirements (Please send M-Print PRO file) |
| Printing method | MC Laser | UL 94 flammability rating | V-2 |
| Width | 27 mm | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |

Datenblatt

SM 27/12.5 SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

