

VG 48-MS68

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG MS (standard brass cable gland), Cable glands, straight, PG 48, 14 mm, OD min. 34 - OD max. 44 mm, IP67, IP68 - 5 bar (30 min.), Brass, nickel-plated
Order No.	1718790000
Type	VG 48-MS68
GTIN (EAN)	4008190352011
Qty.	5 pc(s).

VG 48-MS68

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Length	69 mm	Length (inches)	2.717 inch
Net weight	361.4 g		

Temperatures

Operating temperature	-40 °C...100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (GERMILLOYD)	E-14047
Certificate no. cable gland (UL)	E-199260	Certificate no. cable gland (cULus)	E-199260

General information

AF size	64 mm	AF size 1	64 mm
AF size 2	64 mm	Cable glands	PG, PG 48
Clamp insert	Polyamide	External thread	PG 48
Halogen	Yes	Length of thread	14 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	44 mm	Outer cable diameter, min.	34 mm
Pitch of thread	1.59 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Protection degree with GWDR	IP67, IP68 - 5 bar (30 min.)	Seal insert	CR
Sealing	NBR	Tightening torque	35 Nm
Torque for cap nut, max.	51 Nm	Torque for cap nut, min.	49 Nm
Torque for connecting adapter, max.	36 Nm	Torque for connecting adapter, min.	34 Nm

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Approvals

Approvals



ROHS Conform

Data sheet**VG 48-MS68****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com**Technical data****Downloads**

Approval/Certificate/Document of Conformity	EU Declaration of Conformity - Standard brass nickel plated cable gland DE BS2480 210608 003ISS00
Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	