

## HDC-C-HD-SM0.5AU

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

### General ordering data

Version	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, Conductor cross-section, max.: 0.5, turned, Copper alloy
Order No.	<a href="#">1651630000</a>
Type	HDC-C-HD-SM0.5AU
GTIN (EAN)	4008190400309
Qty.	100 pc(s).

**HDC-C-HD-SM0.5AU**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Diameter	3.5 mm	Net weight	0.66 g
----------	--------	------------	--------

**General data**

Conductor cross-section, max.	0.5 mm <sup>2</sup>	Contact diameter, male Ø	1.6 mm
Contact material	Copper alloy	Cross-section for connected wire	0.5 mm <sup>2</sup>
Material	Copper alloy	Plugging cycles	≥ 500
Production methods	turned	Series	HD
Stripping length, rated connection	8 mm	Surface finish	gold
Type	Male	Type of connection	Crimp connection
Version insert	HD, HDD, HQ, MixMate	Volume resistance	≤4 mΩ

**Classifications**

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ECLASS 9.0	27-44-02-04
ECLASS 9.1	27-44-02-04	ECLASS 10.0	27-44-02-04
ECLASS 11.0	27-44-02-04	ECLASS 12.0	27-44-02-04

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

**HDC-C-HD-SM0.5AU**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

**Drawings**



Leiterquerschnitt	Abisolierlänge
0,14 - 0,37 mm <sup>2</sup>	AWG 26-22 8 mm
0,50 mm <sup>2</sup>	AWG 20 8 mm
0,75 - 1,00 mm <sup>2</sup>	AWG 18 8 mm
1,50 mm <sup>2</sup>	AWG 16 8 mm
2,50 mm <sup>2</sup>	AWG 14 8 mm

