

VT SF 4.5/21 MC NE RT V0


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format



General ordering data

Version	SlimFix, Conductor and cable markers, 4.1 - 4.9 mm, 21 x 7.4 mm, red
Order No.	1730570003
Type	VT SF 4.5/21 MC NE RT V0
GTIN (EAN)	400819095458 1
Qty.	192 Stück
Alternative product	1918990000
compatible printer	2715590000 2438520000 2438510000

VT SF 4.5/21 MC NE RT V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	6.5 mm	Depth (inches)	0.256 inch
Height	21 mm	Height (inches)	0.827 inch
Width	7.4 mm	Width (inches)	0.291 inch
Net weight	0.818 g		

Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

General data

Colour	red	Halogen	No
Material	Polyamide 66	Number of markers per combination	1 MultiCard = Conductor and cable markers
Operating temperature range	-50...120 °C	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Recommended industries	Transportation, Machinery
Size of labelling field	21 x 7.4 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Width	7.4 mm

Conductor and cable markers

Conductor O.D.	4.1 - 4.9 mm	Conductor O.D., max.	4.9 mm
Conductor O.D., min.	4.1 mm	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	4 mm ²	Cross-section for connected wire	4 - 6 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S, EPLAN
Catalogues	Catalogues in PDF-format

VT SF 4.5/21 MC NE RT V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

