


ZQV 6/32 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Version	Accessories, Cross-connector, 41 A
Order No.	1733640000
Type	ZQV 6/32 GE
GTIN (EAN)	4008 190994334
Qty.	10 pc(s).

Creation date March 1, 2023 2:36:43 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

ZQV 6/32 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	33.96 mm	Depth (inches)	1.337 inch
Height	257.3 mm	Height (inches)	10.13 inch
Width	3.1 mm	Width (inches)	0.122 inch
Net weight	45.6 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60
Continuous operating temp., max.	130		

Material data

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	Plugged
---------------------	-----------------	----------------	---------

Cross-connector

Number of cross-connected terminals	32	Rated current, 2-pole	41 A
Rated current, multi-pole	41 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	8.1 mm
-----------------	--------

General

Installation advice	Direct mounting	Number of poles	32
---------------------	-----------------	-----------------	----

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Important note

Product information	Attention: not finger-safe; not suitable for ATEX use Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400V The voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	--

ZQV 6/32 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[EAC certificate](#)

Engineering Data

[CAD data – 26925_ZQV_6-32_GE_DXF.dxf](#)
[CAD data – STEP](#)

Engineering Data

[WSCAD_Zuken E3.S](#)

User Documentation

[Operating instructions_ZDU1.5-ZDU35_ZQV.pdf](#)
[StorageConditionsTerminalBlocks](#)
[BPZL_ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures