

VP M16-EXE SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Version	VPK EX (Ex blanking plug in plastic), Blanking plug, in closed state, M 16, 15 mm, IP66, IP68, Polyamide
Order No.	1737070000
Type	VP M16-EXE SW
GTIN (EAN)	4008190956547
Qty.	100 Stück

Erstellungs-Datum May 30, 2023 2:58:36 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

VP M16-EXE SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	19 mm	Length (inches)	0.748 inch
Diameter	16 mm	Wall thickness, max.	14 mm
Net weight	2.67 g		

Temperatures

Operating temperature	-20 °C...80 °C	Operating temperature, min.	-20 °C
Operating temperature, max.	80 °C		

Technical properties

Protection degree	IP54, IP66
-------------------	------------

Technical data

Colour	Deep black	Protection degree	IP54, IP66
--------	------------	-------------------	------------

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-35	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

VP M16-EXE SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

