

## THM WO 25/140 GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

### General ordering data

Version	THM, Conductor and cable markers, 8.3 - 36.4 mm, 25 x 140 mm, yellow
Order No.	<a href="#">1751561687</a>
Type	THM WO 25/140 GE
GTIN (EAN)	4032248001057
Qty.	1 Stück

Erstellungs-Datum May 22, 2023 11:14:30 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## THM WO 25/140 GE

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	25 mm	Height (inches)	0.984 inch
Width	140 mm	Width (inches)	5.512 inch
Net weight	638 g		

### Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

### General data

Adhesive	Polyacrylate adhesive	Colour	yellow
Halogen	No	Material	Polyester film
Material colour according to resistance code	4	Number of markers per combination	1 Label reel = Conductor and cable markers
Number per roll	1,050	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	26 x 25 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	140 mm		

### Conductor and cable markers

Conductor O.D.	8.3 - 36.4 mm	Conductor O.D., max.	36.4 mm
Conductor O.D., min.	8.3 mm	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Cross-section for connected wire	0.75 - 500 mm <sup>2</sup>
Halogen	No		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**THM WO 25/140 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

