

TM-I 20 MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | TM-I, Insert markers, 20 x 4 mm, To customer specification |
| Order No. | 1680420000 |
| Type | TM-I 20 MC SDR |
| GTIN (EAN) | 4008190487966 |
| Qty. | 80 Stück |
| compatible printer | 2715590000 2438520000 2438510000 |

TM-I 20 MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 2 mm | Depth (inches) | 0.079 inch |
| Height | 20 mm | Height (inches) | 0.787 inch |
| Width | 4 mm | Width (inches) | 0.157 inch |
| Net weight | 0.21 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|--|-----------------------------------|------------------------------|
| Advice label | Colour based on customer requirements (Please send M-Print PRO file) | Colour | To customer specification |
| Colour of printing | black | Halogen | No |
| Material | Polyamide 66 | Number of markers per combination | 1 MultiCard = Insert markers |
| Operating temperature range | -40...100 °C | Operating temperature range, max. | 100 °C |
| Operating temperature range, min. | -40 °C | Orientation of print | horizontal |
| Printed characters | Based on customer requirements (Please send M-Print PRO file) | Printing method | MC Laser |
| Type of printing | To customer specification | UL 94 flammability rating | V-2 |
| Width | 4 mm | | |

Conductor and cable markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |