

HDC-C-M20-SCG0.08-0.2AU**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	Heavy-duty connectors, Crimp contact, CM 20, Pin, Conductor cross-section, max.: 0.2, punched, Copper alloy
Order No.	1682420000
Type	HDC-C-M20-SCG0.08-0.2AU
GTIN (EAN)	4008190859930
Qty.	500 pc(s).

HDC-C-M20-SCG0.08-0.2AU

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.224 g

General data

Conductor cross-section, max.	0.2 mm ²	Conductor cross-section, min.	0.08 mm ²
Contact diameter, male Ø	1 mm	Contact material	Copper alloy
Cross-section for connected wire	0.08 - 0.2 mm ²	Material	Copper alloy
Production methods	punched	Stripping length, rated connection	2.5 mm
Surface finish	gold	Type	Pin
Type of connection	Crimp connection	Version insert	CM 20
Volume resistance	≤5 mΩ		

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ECLASS 9.0	27-44-02-04
ECLASS 9.1	27-44-02-04	ECLASS 10.0	27-44-02-04
ECLASS 11.0	27-44-02-04	ECLASS 12.0	27-44-02-04

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

HDC-C-M20-SCG0.08-0.2AU

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Drawings



Leiterquerschnitt	Abisolierlänge
-------------------	----------------

0,08 - 0,20 mm ² AWG 28-24	2,5+0,5 mm
---------------------------------------	------------

0,20 - 0,52 mm ² AWG 24-20	2,5+0,5 mm
---------------------------------------	------------

