

**HDC-C-M20-BCG0.08-0.2AU****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	Heavy-duty connectors, Crimp contact, CM 20, Female, Conductor cross-section, max.: 0.2, punched, Copper alloy
Order No.	<a href="#">1682430000</a>
Type	HDC-C-M20-BCG0.08-0.2AU
GTIN (EAN)	4008190859954
Qty.	500 pc(s).

**HDC-C-M20-BCG0.08-0.2AU**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0.252 g

**General data**

Conductor cross-section, max.	0.2 mm <sup>2</sup>	Conductor cross-section, min.	0.08 mm <sup>2</sup>
Contact diameter, male Ø	1 mm	Contact material	Copper alloy
Cross-section for connected wire	0.08 - 0.2 mm <sup>2</sup>	Material	Copper alloy
Production methods	punched	Stripping length, rated connection	2.5 mm
Surface finish	gold	Type	Female
Type of connection	Crimp connection	Version insert	CM 20
Volume resistance	≤5 mΩ		

**Classifications**

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ECLASS 9.0	27-44-02-04
ECLASS 9.1	27-44-02-04	ECLASS 10.0	27-44-02-04
ECLASS 11.0	27-44-02-04	ECLASS 12.0	27-44-02-04

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>

**HDC-C-M20-BCG0.08-0.2AU**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

**Drawings**



Leiterquerschnitt	Abisolierlänge
-------------------	----------------

0,08 - 0,20 mm <sup>2</sup> AWG 28-24	2,5+0,5 mm
---------------------------------------	------------

0,20 - 0,52 mm <sup>2</sup> AWG 24-20	2,5+0,5 mm
---------------------------------------	------------

