

LM MT300 56/22 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

Version	LaserMark, Device markers, 22 x 56 mm, white
Order No.	1686421044
Type	LM MT300 56/22 WS
GTIN (EAN)	4008 190494094
Qty.	10 Stück

Erstellungs-Datum May 16, 2023 4:19:23 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

LM MT300 56/22 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	22 mm	Height (inches)	0.866 inch
Width	56 mm	Width (inches)	2.205 inch
Net weight	11.6 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester, PVC-free	Material colour according to resistance code	9
Number of markers per combination	1 Label sheet = 36 Device markers	Number per sheet	36
Operating temperature range	-40...150 °C	Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C	Printing method	Laser print
UL 94 flammability rating	HB	Version	Self-adhesive
Width	56 mm		

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

LM MT300 56/22 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

