


LM WO 23/55 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	LaserMark, Conductor and cable markers, 6.8 - 12 mm, 23 x 55 mm, white
Order No.	1695721044
Type	LM WO 23/55 WS
GTIN (EAN)	4008 190924676
Qty.	10 Stück

Erstellungs-Datum May 16, 2023 4:25:20 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

LM WO 23/55 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	23 mm	Height (inches)	0.906 inch
Width	55 mm	Width (inches)	2.165 inch
Net weight	10.1 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate	Colour	white
Halogen	No	Material	Polyester film
Material colour according to resistance code	9	Number of markers per combination	1 Label sheet = 40 Conductor and cable markers
Number per sheet	40	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	23 x 12.7 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	55 mm		

Conductor and cable markers

Conductor O.D.	6.8 - 12 mm	Conductor O.D., max.	12 mm
Conductor O.D., min.	6.8 mm	Conductor cross-section, max.	50 mm ²
Conductor cross-section, min.	10 mm ²	Cross-section for connected wire	10 - 50 mm ²
Halogen	No	Text field height	12.5 mm
Text field width	22.8 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S, EPLAN
Catalogues	Catalogues in PDF-format

