

**LM WO 25/68 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Self-adhesive polyester labels which are suitable for A4 office laser printer.

**General ordering data**

Version	LaserMark, Conductor and cable markers, 8.2 - 14.3 mm, 25 x 68 mm, white
Order No.	<a href="#">1695731044</a>
Type	LM WO 25/68 WS
GTIN (EAN)	4008 190924706
Qty.	10 Stück

Erstellungs-Datum May 16, 2023 4:25:38 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## LM WO 25/68 WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	25 mm	Height (inches)	0.984 inch
Width	68 mm	Width (inches)	2.677 inch
Net weight	10 g		

### Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

### General data

Adhesive	Acrylate	Colour	white
Halogen	No	Material	Polyester film
Material colour according to resistance code	9	Number of markers per combination	1 Label sheet = 28 Conductor and cable markers
Number per sheet	28	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	25 x 17 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	68 mm		

### Conductor and cable markers

Conductor O.D.	8.2 - 14.3 mm	Conductor O.D., max.	14.3 mm
Conductor O.D., min.	8.2 mm	Conductor cross-section, max.	70 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Cross-section for connected wire	16 - 70 mm <sup>2</sup>
Halogen	No	Text field height	17 mm
Text field width	25.4 mm		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

