

## LM WO 25/140 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

Self-adhesive polyester labels which are suitable for A4 office laser printer.

### General ordering data

|            |   |
|------------|---|
| Version    | LaserMark, Conductor and cable markers, 16.2 - 36.4 mm, 25 x 140 mm, yellow |
| Order No.  | <a href="#">1712491687</a>  |
| Type       | LM WO 25/140 GE   |
| GTIN (EAN) | 4008 190947125  |
| Qty.       | 10 Stück  |

Erstellungs-Datum May 16, 2023 4:29:21 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## LM WO 25/140 GE

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 0.025 mm | Depth (inches)  | 0.001 inch |
| Height     | 25 mm    | Height (inches) | 0.984 inch |
| Width      | 140 mm   | Width (inches)  | 5.512 inch |
| Net weight | 10.4 g   |                 |            |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

### General data

|  |            |                                   |  |
|--|------------|-----------------------------------|--|
| Adhesive                                     | Acrylate   | Colour                            | yellow   |
| Halogen                                      | No         | Material                          | Polyester film                                 |
| Material colour according to resistance code | 4          | Number of markers per combination | 1 Label sheet = 16 Conductor and cable markers |
| Number per sheet                             | 16         | Operating temperature range       | -40...150 °C                                   |
| Operating temperature range, max.            | 150 °C     | Operating temperature range, min. | -40 °C   |
| Size of labelling field                      | 25 x 26 mm | Type of printing                  | neutral  |
| UL 94 flammability rating                    | V-0        | Version                           | Self-adhesive                                  |
| Width  | 140 mm     |                                   |  |

### Conductor and cable markers

|                               |                    |                                  |                          |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 16.2 - 36.4 mm     | Conductor O.D., max.             | 36.4 mm                  |
| Conductor O.D., min.          | 16.2 mm            | Conductor cross-section, max.    | 150 mm <sup>2</sup>      |
| Conductor cross-section, min. | 70 mm <sup>2</sup> | Cross-section for connected wire | 70 - 150 mm <sup>2</sup> |
| Halogen                       | No                 | Text field height                | 26 mm                    |
| Text field width              | 25 mm              |                                  |                          |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">WSCAD, Zuken E3.S, EPLAN</a> |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**Datenblatt**

**LM WO 25/140 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

