

WSM 10 2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

WSM small plates

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, .., ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

General ordering data

| | |
|------------|--|
| Version | Stainless steel markers, Conductor and cable markers, 5.5 x 9.9 mm, silver |
| Order No. | 1712500002 |
| Type | WSM 10 2 |
| GTIN (EAN) | 4008 190947200 |
| Qty. | 200 Stück |

Erstellungs-Datum May 16, 2023 4:29:40 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

WSM 10 2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.3 mm | Depth (inches) | 0.012 inch |
| Height | 5.5 mm | Height (inches) | 0.217 inch |
| Width | 9.9 mm | Width (inches) | 0.39 inch |
| Net weight | 0.13 g | | |

Temperatures

| | |
|-----------------------------|--------|
| Operating temperature range | 500 °C |
|-----------------------------|--------|

General data

| | | | |
|-----------------------------------|--|--|------------|
| Colour | silver | Halogen | No |
| Material | Stainless steel 1.4404 | Material colour according to resistance code | 0 |
| Number of markers per combination | 1 Component part = Conductor and cable markers | Operating temperature range | 500 °C |
| Operating temperature range, max. | 500 °C | Orientation of print | horizontal |
| Printed characters | Numbers | Printing | 2 |
| Type of printing | Standard | Width | 9.9 mm |

Conductor and cable markers

| | | | |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Conductor cross-section, max. | 500 mm ² | Conductor cross-section, min. | 16 mm ² |
| Cross-section for connected wire | 16 - 500 mm ² | Halogen | No |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |