

## WSM 10 O

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

### WSM small plates

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, .., ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

### General ordering data

|            |  |
|------------|--|
| Version    | Stainless steel markers, Conductor and cable markers, 5.5 x 9.9 mm, silver |
| Order No.  | <a href="#">1712501665</a>   |
| Type       | WSM 10 O   |
| GTIN (EAN) | 4008 190947422   |
| Qty.       | 200 Stück  |

Erstellungs-Datum May 16, 2023 4:33:39 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## WSM 10 O

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 0.3 mm | Depth (inches)  | 0.012 inch |
| Height     | 5.5 mm | Height (inches) | 0.217 inch |
| Width      | 9.9 mm | Width (inches)  | 0.39 inch  |
| Net weight | 0.15 g |                 |            |

### Temperatures

|                             |        |
|-----------------------------|--------|
| Operating temperature range | 500 °C |
|-----------------------------|--------|

### General data

|                             |                        |                                   |  |
|-----------------------------|------------------------|-----------------------------------|--|
| Colour                      | silver                 | Halogen                           | No   |
| Material                    | Stainless steel 1.4404 | Number of markers per combination | 1 Component part = Conductor and cable markers |
| Operating temperature range | 500 °C                 | Operating temperature range, max. | 500 °C   |
| Orientation of print        | horizontal             | Printed characters                | Upper-case letters                             |
| Printing                    | 0                      | Type of printing                  | Standard                                       |
| Width                       | 9.9 mm                 |                                   |  |

### Conductor and cable markers

|                                  |                          |                               |                    |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Conductor cross-section, max.    | 500 mm <sup>2</sup>      | Conductor cross-section, min. | 16 mm <sup>2</sup> |
| Cross-section for connected wire | 16 - 500 mm <sup>2</sup> | Halogen                       | No                 |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">WSCAD, EPLAN</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |