

WSM 10 NEUTRAL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

General ordering data

| | |
|------------|--|
| Version | Stainless steel markers, Conductor and cable markers, 5.5 x 9.9 mm, silver |
| Order No. | 1712502000 |
| Type | WSM 10 NEUTRAL |
| GTIN (EAN) | 4032248052844 |
| Qty. | 200 Stück |

WSM 10 NEUTRAL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.3 mm | Depth (inches) | 0.012 inch |
| Height | 5.5 mm | Height (inches) | 0.217 inch |
| Width | 9.9 mm | Width (inches) | 0.39 inch |
| Net weight | 0.13 g | | |

Temperatures

| | |
|-----------------------------|--------|
| Operating temperature range | 250 °C |
|-----------------------------|--------|

General data

| | | | |
|-----------------------------------|--|-----------------------------|------------------------|
| Colour | silver | Material | Stainless steel 1.4404 |
| Number of markers per combination | 1 Component part = Conductor and cable markers | Operating temperature range | 250 °C |
| Operating temperature range, max. | 250 °C | Type of printing | neutral |
| Width | 9.9 mm | | |

Conductor and cable markers

| | | | |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Conductor cross-section, max. | 500 mm ² | Conductor cross-section, min. | 16 mm ² |
| Cross-section for connected wire | 16 - 500 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |