

**SAIS-M-5/8S M12 5P A-COD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

**General ordering data**

Version	Field attachable connector, M12, pin, straight
Order No.	<a href="#">1784740000</a>
Type	SAIS-M-5/8S M12 5P A-COD
GTIN (EAN)	4032248191826
Qty.	1 pc(s).

Creation date February 15, 2023 4:30:55 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

**SAIS-M-5/8S M12 5P A-COD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 46 g

**Temperatures**

Operating temperature, min. -40 °C Operating temperature, max. 85 °C

**Technical data customisable plug-in connectors**

Cable diameter, max.	8 mm	Cable diameter, min.	6 mm
Coding	A	Conductor cross-section, max.	0.75 mm <sup>2</sup>
Conductor cross-section, min.	0.14 mm <sup>2</sup>	Connection cross-section, max.	0.75 mm <sup>2</sup>
Connection cross-section, min.	0.14 mm <sup>2</sup>	Contact surface	Gold-plated
Housing main material	CuZn	Insulation strength	10 <sup>8</sup> Ω
Number of poles	5	Plugging cycles	≥ 100
Pollution severity	3	Protection degree	IP67
Rated current	4 A	Rated voltage	60 V
Rated voltage	250 V (4-pole) / 60 V (5-pole) / 30 V (8-pole)	Shield connection	Yes
Temperature range of housing	-40 ... +85 °C	Threaded ring material	Diecast zinc
Type of connection	Screw connection		

**General Info**

Number of poles	5	Connection 1	M12
Connection 2	Screw	Description of article	SAISM / SAIBM
Housing main material	CuZn	Connection thread	M12
Contact surface	Gold-plated	Protection degree	IP67
Plugging cycles	≥ 100		

**Standards**

Connector standard IEC 61076-2-101

**Classifications**

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16

**Environmental Product Compliance**REACH SVHC Lead 7439-92-1 Imidazolidine-2-thione 96-45-7  
SCIP bcee35cf-c0f5-43d2-8daf-65ab0d08641a**Approvals**

Approvals

ROHS Conform  
UL File Number Search UL Website  
Certificate No. (cURus) E307231

Creation date February 15, 2023 4:30:55 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

**SAIS-M-5/8S M12 5P A-COD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

**SAIS-M-5/8S M12 5P A-COD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Pole scheme**

