

**CB 200/3,5 NC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

|            |   |
|------------|---|
| Version    | Cable ties, 3.5 x 200 mm, Polyamide 66, 180 N |
| Order No.  | <a href="#">1720630000</a>                    |
| Type       | CB 200/3,5 NC                                 |
| GTIN (EAN) | 4008190362317                                 |
| Qty.       | 100 Stück                                     |

Erstellungs-Datum May 30, 2023 2:46:54 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## CB 200/3,5 NC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 1.25 mm | Depth (inches)  | 0.049 inch |
| Height     | 200 mm  | Height (inches) | 7.874 inch |
| Width      | 3.5 mm  | Width (inches)  | 0.138 inch |
| Net weight | 0.929 g |                 |            |

### Temperatures

|                             |             |                             |        |
|-----------------------------|-------------|-----------------------------|--------|
| Operating temperature range | -40...85 °C | Operating temperature, min. | -40 °C |
| Operating temperature, max. | 85 °C       |                             |        |

### Installation materials

|                                   |       |                                   |              |
|-----------------------------------|-------|-----------------------------------|--------------|
| Bundle diameter, max.             | 50 mm | Bundle diameter, min.             | 3 mm         |
| Cable diameter, max.              | 50 mm | For re-opening                    | No           |
| Halogen                           | No    | Material                          | Polyamide 66 |
| Operating temperature range, max. | 85 °C | Operating temperature range, min. | -40 °C       |
| Tensile strength                  | 180 N | Tensile strength (Pound-force)    | 40 lbf       |
| UL 94 flammability rating         | V-2   | UV-resistant                      | No           |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000046    | ETIM 7.0    | EC000046    |
| ETIM 8.0    | EC000046    | ECLASS 9.0  | 27-14-07-02 |
| ECLASS 9.1  | 27-14-07-02 | ECLASS 10.0 | 27-14-07-02 |
| ECLASS 11.0 | 27-14-07-02 | ECLASS 12.0 | 27-14-07-02 |

### Approvals

Approvals



|                       |            |
|-----------------------|------------|
| ROHS                  | Conform    |
| UL File Number Search | UL Website |
| Certificate No. (UR)  | E317499    |

### Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">DE PI830000 160627 001</a>   |
| Engineering Data                            | <a href="#">WSCAD, EPLAN</a>             |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a> |

**Datenblatt**

**CB 200/3,5 NC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

