


VT SF 6/21 MC NE GN V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

| | |
|--------------------|--|
| Version | SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm, green |
| Order No. | 1730560005 |
| Type | VT SF 6/21 MC NE GN V0 |
| GTIN (EAN) | 403224855 1668 |
| Qty. | 160 Stück |
| compatible printer | 2715590000 2438520000 2438510000 |

VT SF 6/21 MC NE GN V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 8.5 mm | Depth (inches) | 0.335 inch |
| Height | 21 mm | Height (inches) | 0.827 inch |
| Width | 8.4 mm | Width (inches) | 0.331 inch |
| Net weight | 0.975 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -50...120 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|---|
| Colour | green | Halogen | No |
| Material | Polyamide 66 | Number of markers per combination | 1 MultiCard = Conductor and cable markers |
| Operating temperature range | -50...120 °C | Operating temperature range, max. | 120 °C |
| Operating temperature range, min. | -50 °C | Recommended industries | Transportation, Machinery |
| Size of labelling field | 21 x 8.4 mm | Type of printing | neutral |
| UL 94 flammability rating | V-0 | Width | 8.4 mm |

Conductor and cable markers

| | | | |
|-------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D. | 5.8 - 7.8 mm | Conductor O.D., max. | 7.8 mm |
| Conductor O.D., min. | 5.8 mm | Conductor cross-section, max. | 16 mm ² |
| Conductor cross-section, min. | 10 mm ² | Cross-section for connected wire | 10 - 16 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S, EPLAN |
| Catalogues | Catalogues in PDF-format |

VT SF 6/21 MC NE GN V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

