

TM 205/18 V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

General ordering data

| | |
|------------|--|
| Version | TM, Socket x 14 mm, PVC, Colour: Transparent, Conductor O.D.: 10 - 14 mm |
| Order No. | 1806310000 |
| Type | TM 205/18 V0 |
| GTIN (EAN) | 4032248275823 |
| Qty. | 200 Stück |

Erstellungs-Datum May 22, 2023 11:39:14 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

TM 205/18 V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 14 mm | Depth (inches) | 0.551 inch |
| Height | 18 mm | Height (inches) | 0.709 inch |
| Width | 14 mm | Width (inches) | 0.551 inch |
| Net weight | 1.115 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|-----------------------------------|-------------|-----------------------------------|---------------------------|
| Colour | Transparent | Material | PVC |
| Operating temperature range | -40...80 °C | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -40 °C | Recommended industries | Transportation, Machinery |
| Type of printing | neutral | UL 94 flammability rating | V-0 |
| Width | 14 mm | | |

Conductor and cable markers

| | | | |
|-------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D. | 10 - 14 mm | Conductor O.D., max. | 14 mm |
| Conductor O.D., min. | 10 mm | Conductor cross-section, max. | 35 mm ² |
| Conductor cross-section, min. | 16 mm ² | Cross-section for connected wire | 16 - 35 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S, EPLAN |
| Product Change Notification | PCN Transparent Sleeves_DE PCN Transparent Sleeves_EN |
| Catalogues | Catalogues in PDF-format |