

## CLI M 2-4 GE/SW G MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

### General ordering data

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 10 - 317 mm, 4 x 11.3 mm, yellow |
| Order No.  | <a href="#">1733651649</a>   |
| Type       | CLI M 2-4 GE/SW G MP   |
| GTIN (EAN) | 4008 190398118   |
| Qty.       | 100 Stück  |

Erstellungs-Datum May 22, 2023 10:17:14 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CLI M 2-4 GE/SW G MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 3 mm    | Depth (inches)  | 0.118 inch |
| Height     | 4 mm    | Height (inches) | 0.157 inch |
| Width      | 11.3 mm | Width (inches)  | 0.445 inch |
| Net weight | 0.12 g  |                 |            |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### General data

|  |                    |                                   |  |
|--|--------------------|-----------------------------------|--|
| Colour                                       | yellow             | Colour of printing                | black  |
| Halogen                                      | Yes                | Material                          | PVC, soft, without Cadmium                     |
| Material colour according to resistance code | 4                  | Number of markers per combination | 1 Component part = Conductor and cable markers |
| Operating temperature range                  | -30...80 °C        | Operating temperature range, max. | 80 °C  |
| Operating temperature range, min.            | -30 °C             | Orientation of print              | horizontal                                     |
| Printed characters                           | Upper-case letters | Printing                          | G  |
| Printing method                              | hot-embossing      | Recommended industries            | Process, Machinery                             |
| Type of printing                             | Standard           | UL 94 flammability rating         | V-0  |
| Version                                      | MultiPack          | Width                             | 11.3 mm  |

### Conductor and cable markers

|                               |                    |                                  |                          |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 10 - 317 mm        | Conductor O.D., max.             | 317 mm                   |
| Conductor O.D., min.          | 10 mm              | Conductor cross-section, max.    | 500 mm <sup>2</sup>      |
| Conductor cross-section, min. | 16 mm <sup>2</sup> | Cross-section for connected wire | 16 - 500 mm <sup>2</sup> |
| Halogen                       | Yes                |                                  |                          |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">WSCAD, EPLAN</a>   |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

**Datenblatt**

**CLI M 2-4 GE/SW G MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**



Similar to illustration