

KLBU CO 4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



Shielding and earthing

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1749161001
Type	KLBU CO 4
GTIN (EAN)	4032248064458
Qty.	10 Stück

KLBUE CO 4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	56 mm	Depth (inches)	2.205 inch
Height	32 mm	Height (inches)	1.26 inch
Width	25 mm	Width (inches)	0.984 inch
Mounting dimension - width	31 mm	Net weight	53.252 g

Temperatures

Storage temperature -25 °C...55 °C

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version For a shield connection

Additional technical data

Explosion-tested version	No	Installation advice	Busbar
Type of fixing	Snap-on		

Conductors for clamping (rated connection)

Cable diameter, max.	28 mm	Cable diameter, min.	15 mm
----------------------	-------	----------------------	-------

Dimensions

Pitch in mm (P) 25 mm

General

Installation advice Busbar

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

Approvals

Approvals



ROHS Conform

KLBUE CO 4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	