

VT SF 0/12 MC NE GE V0


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format



General ordering data

Version	SlimFix, Conductor and cable markers, 1.2 - 1.6 mm, 12 x 3.2 mm, yellow
Order No.	1752110004
Type	VT SF 0/12 MC NE GE V0
GTIN (EAN)	4032248002948
Qty.	800 Stück
compatible printer	2715590000 2438520000 2438510000

VT SF 0/12 MC NE GE V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	3.2 mm	Depth (inches)	0.126 inch
Height	12 mm	Height (inches)	0.472 inch
Width	3.2 mm	Width (inches)	0.126 inch
Net weight	0.159 g		

Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

General data

Colour	yellow	Halogen	No
Material	Polyamide 66	Material colour according to resistance code	4
Number of markers per combination	1 MultiCard = Conductor and cable markers	Operating temperature range	-50...120 °C
Operating temperature range, max.	120 °C	Operating temperature range, min.	-50 °C
Recommended industries	Transportation, Machinery	Size of labelling field	12 x 3.2 mm
Type of printing	neutral	UL 94 flammability rating	V-0
Width	3.2 mm		

Conductor and cable markers

Conductor O.D.	1.2 - 1.6 mm	Conductor O.D., max.	1.6 mm
Conductor O.D., min.	1.2 mm	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.25 mm ²	Cross-section for connected wire	0.25 - 0.5 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S, EPLAN
Catalogues	Catalogues in PDF-format

Datenblatt

VT SF 0/12 MC NE GE V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

