

SAIB-M23-19P-ST-80M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

The M23 cables offer: high mating frequency, high current carrying capacity and high-density contacts coupled with minimal dimensions.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

| | |
|------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version | Sensor/actuator line, One end without connector, M23, Number of poles: 19, 80 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No. | 1818188000 |
| Type | SAIB-M23-19P-ST-80M |
| GTIN (EAN) | 4050118343687 |
| Qty. | 1 pc(s). |

Creation date March 16, 2023 5:16:12 PM CET

SAIB-M23-19P-ST-80M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|---------|
| Net weight | 8,000 g |
|------------|---------|

Temperatures

| | | | |
|-----------------------------|--------|-----------------------------|-------|
| Operating temperature, min. | -25 °C | Operating temperature, max. | 80 °C |
|-----------------------------|--------|-----------------------------|-------|

Technical specifications for cable

| | | | |
|--------------------------------------|------------------------------------------------------|------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Bending cycles | 2 Mio | Bending radius, min., moving | 10 x cable diameter |
| Cable length | 80 m | Colour coding | violet, red, grey, red / blue, green, blue, grey / pink, white / green, white / yellow, white / grey, black, Green/yellow, Yellow / brown, brown / green, white, yellow, pink, grey / brown, brown |
| Core in accordance with UL AWM style | 10493 (80 °C / 300 V) | Halogen | No |
| Insulation | TPM | Irradiation crosslinked | No |
| Number of poles | 19 | Outer cladding in accordance with UL AWM style | 21198 (80 °C / 300 V) |
| Outside diameter | 9.1 mm ± 0.3 mm | Resistant to welding beads | No |
| Sheath material | PUR | Sheathing colour | black |
| Shielded | No | Suitable for cable carriers | Yes |
| Temperature range, moving | -25...80 °C | Temperature range, stationary | -50...80 °C |
| Torsion resistance | 0 °/m | Welding spark resistance | No |
| Wire cross section (Print/Online) | 3 x 0.75 mm ² + 16 x 0.34 mm ² | | |

General technical data

| | | |
|------------------------------|-------------------------------------|--------------|
| Connection side version | Connection side | 1 |
| | Connection thread | M23 |
| | Type of contact | Socket |
| | Type of thread | Inner thread |
| | Outlet direction | straight |
| Connection side version 1 | M23, Socket, Inner thread, straight | |
| Connection thread | M23 | |
| Contact surface | Gold-plated | |
| Housing main material | PUR | |
| Insulation strength | 10 ¹² Ω | |
| LED | No | |
| Plugging cycles | ≥ 50 | |
| Pollution severity | 2 | |
| Protection degree | IP67 | |
| Rated current | 8 A | |
| Rated voltage | 120 V | |
| Temperature range of housing | -25...+80 °C | |
| Threaded ring material | Diecast zinc | |
| Tightening torque | M23: 2.5 Nm | |
| Version | Female socket, straight | |
| jumpered | No | |

SAIB-M23-19P-ST-80M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Electrical properties**

| | | | |
|---------------------|--------------------|---------------|-------|
| Insulation strength | 10 ¹² Ω | Rated voltage | 120 V |
|---------------------|--------------------|---------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001855 | ETIM 7.0 | EC001855 |
| ETIM 8.0 | EC001855 | ECLASS 9.0 | 27-06-03-11 |
| ECLASS 9.1 | 27-06-03-11 | ECLASS 10.0 | 27-06-03-11 |
| ECLASS 11.0 | 27-06-03-11 | ECLASS 12.0 | 27-06-03-11 |

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------------------|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN |

SAIB-M23-19P-ST-80M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com


Drawings

Dimensioned drawing



Straight socket

Pole scheme



Socket

Wiring diagram



The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F