

LM WO 25.4/57 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

| | |
|------------|---|
| Version | LaserMark, Conductor and cable markers, 6.8 - 12 mm, 25.4 x 57 mm, yellow |
| Order No. | 1768390000 |
| Type | LM WO 25.4/57 GE |
| GTIN (EAN) | 4032248110032 |
| Qty. | 10 Stück |

Erstellungs-Datum May 22, 2023 11:26:46 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

LM WO 25.4/57 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 0.025 mm | Depth (inches) | 0.001 inch |
| Height | 25.4 mm | Height (inches) | 1 inch |
| Width | 57 mm | Width (inches) | 2.244 inch |
| Net weight | 10.1 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

General data

| | | | |
|--|--------------|-----------------------------------|--|
| Adhesive | Acrylate | Colour | yellow |
| Halogen | No | Material | Polyester film |
| Material colour according to resistance code | 4 | Number of markers per combination | 1 Label sheet = 35 Conductor and cable markers |
| Number per sheet | 35 | Operating temperature range | -40...150 °C |
| Operating temperature range, max. | 150 °C | Operating temperature range, min. | -40 °C |
| Size of labelling field | 25.4 x 18 mm | Type of printing | neutral |
| UL 94 flammability rating | V-0 | Version | Self-adhesive |
| Width | 57 mm | | |

Conductor and cable markers

| | | | |
|-------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D. | 6.8 - 12 mm | Conductor O.D., max. | 12 mm |
| Conductor O.D., min. | 6.8 mm | Conductor cross-section, max. | 50 mm ² |
| Conductor cross-section, min. | 10 mm ² | Cross-section for connected wire | 10 - 50 mm ² |
| Halogen | No | Text field height | 18.5 mm |
| Text field width | 25.4 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S, EPLAN |
| Catalogues | Catalogues in PDF-format |

Datenblatt

LM WO 25.4/57 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

