

WDU 10 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

General ordering data

| | |
|------------|---|
| Version | Feed-through terminal, Screw connection, 10 mm ² , 1000 V, 57 A, white |
| Order No. | 1833380000 |
| Type | WDU 10 WS |
| GTIN (EAN) | 4050118044904 |
| Qty. | 50 pc(s). |

Creation date March 3, 2023 11:20:21 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

WDU 10 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------------------------|------------|----------------|------------|
| Depth | 46.5 mm | Depth (inches) | 1.831 inch |
| Depth including DIN rail | 47 mm | Height | 60 mm |
| Height (inches) | 2.362 inch | Width | 9.9 mm |
| Width (inches) | 0.39 inch | Net weight | 17.88 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|-------|
| Material | Wemid | Colour | white |
| UL 94 flammability rating | V-0 | | |

Rating data IECEx/ATEX

| | | | |
|--------------------------------|--------------------|---------------------------------|--------------------|
| Certificate No. (ATEX) | DEMKO14ATEX1338U | Certificate No. (IECEX) | IECEXULD14.0005U |
| Max. voltage (ATEX) | 690 V | Current (ATEX) | 57 A |
| Wire cross section max. (ATEX) | 10 mm ² | Max. voltage (IECEX) | 690 V |
| Current (IECEX) | 57 A | Wire cross section max. (IECEX) | 10 mm ² |
| Marking EN 60079-7 | Ex eb II C Gb | Ex 2014/34/EU label | II 2 G D |

System specifications

| | | | |
|-------------------------------------|---|-------------------------------|-----|
| Version | Screw connection, for screwable cross-connection, One end without connector | End cover plate required | Yes |
| Number of potentials | 1 | Number of levels | 1 |
| Number of clamping points per level | 2 | Number of potentials per tier | 1 |
| Levels cross-connected internally | No | PE connection | No |
| Rail | TS 35 | N-function | No |
| PE function | No | PEN function | No |

Additional technical data

| | |
|------------------|---------|
| Type of mounting | Snap-on |
|------------------|---------|

CSA rating data

| | | | |
|-------------------------------|----------------|-------------------------------|-------|
| Certificate No. (CSA) | 200039-1057876 | Current size C (CSA) | 65 A |
| Voltage size C (CSA) | 600 V | Wire cross section max. (CSA) | 6 AWG |
| Wire cross section min. (CSA) | 18 AWG | | |

WDU 10 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Conductors for clamping (rated connection)

| Clampable conductor | Connection specification | Screw connection | | |
|--|--|--|---------------------|-----------------------|
| | Cross-section for conductor connection | Type | solid, H05(07) V-U | |
| | | min. | 1.5 mm ² | |
| | | max. | 16 mm ² | |
| | | nominal | 10 mm ² | |
| | wire end ferrule | Stripping length | min. | 12 mm |
| | | | max. | 12 mm |
| | | | nominal | 12 mm |
| | | Tightening torque | min. | 1.2 Nm |
| | | | max. | 1.9 Nm |
| | | Recommended wire-end ferrule | | |
| | | Cross-section for conductor connection | Type | stranded, H07V-R |
| | | | min. | 1.5 mm ² |
| max. | | | 16 mm ² | |
| nominal | | | 10 mm ² | |
| wire end ferrule | | Stripping length | min. | 12 mm |
| | | | max. | 12 mm |
| | | | nominal | 12 mm |
| | | Tightening torque | min. | 1.2 Nm |
| | | | max. | 1.9 Nm |
| | | Recommended wire-end ferrule | | |
| | | Cross-section for conductor connection | Type | flexible, H05(07) V-K |
| | | | min. | 1.5 mm ² |
| | max. | | 16 mm ² | |
| | nominal | | 10 mm ² | |
| | wire end ferrule | Stripping length | min. | 12 mm |
| | | | max. | 12 mm |
| | | | nominal | 12 mm |
| | | Tightening torque | min. | 1.2 Nm |
| | | | max. | 1.9 Nm |
| | | Recommended wire-end ferrule | | |
| | Clamping range, max. | 16 mm ² | | |
| | Clamping range, min. | 1.31 mm ² | | |
| Clamping screw | M 4 | | | |
| Connection cross-section, stranded, max. | 16 mm ² | | | |
| Connection cross-section, stranded, min. | 1.5 mm ² | | | |
| Connection direction | on side | | | |
| Number of connections | 2 | | | |
| Stripping length | 12 mm | | | |
| Tightening torque, max. | 1.9 Nm | | | |
| Tightening torque, min. | 1.2 Nm | | | |
| Twin wire-end ferrules, max. | 6 mm ² | | | |
| Twin wire-end ferrules, min. | 1.5 mm ² | | | |
| Type of connection | Screw connection | | | |
| Wire connection cross section AWG, max. | AWG 6 | | | |
| Wire connection cross section AWG, min. | AWG 16 | | | |
| Wire connection cross section, finely stranded, max. | 16 mm ² | | | |

Creation date March 3, 2023 11:20:21 AM CET

WDU 10 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | |
|---|---------------------|
| Wire connection cross section, finely stranded, min. | 1.5 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 16 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 1.5 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 16 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 1.5 mm ² |
| Wire connection cross-section, solid core, max. | 16 mm ² |
| Wire connection cross-section, solid core, min. | 1.5 mm ² |

General

| | | | |
|---|--------|---|-------|
| Rail | TS 35 | Wire connection cross section AWG, max. | AWG 6 |
| Wire connection cross section AWG, min. | AWG 16 | | |

Rating data

| | | | |
|--|--------------------|---|---------|
| Rated cross-section | 10 mm ² | Rated voltage | 1,000 V |
| Rated DC voltage | 1,000 V DC | Rated current | 57 A |
| Volume resistance according to IEC 60947-7-x | 0.56 mΩ | Power loss in accordance with IEC 60947-7-x | 1.82 W |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000897 | ETIM 7.0 | EC000897 |
| ETIM 8.0 | EC000897 | ECLASS 9.0 | 27-14-11-20 |
| ECLASS 9.1 | 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| ECLASS 11.0 | 27-14-11-20 | ECLASS 12.0 | 27-14-11-20 |

Approvals

Approvals



ROHS Conform

WDU 10 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | Attestation of Conformity IECEX Certificate CB Testreport CB Certificate EAC certificate INMETRO certificate POLSKIREJ certificate EAC EX Certificate CCC Ex Certificate UKCA Ex Certificate CE Declaration of Conformity ATEX Certificate CE Declaration of Conformity all terminals UKCA declaration of conformity |
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| User Documentation | NTI_IECEX_WDU-WPE 10.pdf StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |

Data sheet

WDU 10 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

