

VG M50 - K 68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, M 50, 18 mm, OD min. 30 - OD max. 38 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	1772340000
Type	VG M50 - K 68
GTIN (EAN)	4032248130009
Qty.	10 pc(s).

Creation date March 9, 2023 11:59:17 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

VG M50 - K 68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	71 mm	Length (inches)	2.795 inch
Net weight	94.6 g		

Temperatures

Operating temperature	-40 °C...100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (UL)	E-199260 - BM 19
Certificate no. cable gland (cULus)	E-199260 - BM 19		

General information

AF size	60 mm	AF size 1	60 mm
Cable glands	metric	External thread	M 50
Halogen	Yes	Length of thread	18 mm
Material		Note: protection class	IP66 applications only possible with sealing ring for threaded connections. Without sealing ring for threaded connections, only IP54 is possible.
	Polyamide 6		
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	38 mm	Outer cable diameter, min.	30 mm
Pitch of thread		Protection degree	IP67, IP68 - 5 bar (30 min.)
	1.5 mm	Seal insert	CR
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Standards	EN/IEC 62444
Silicone	No	Torque for cap nut, max.	20 Nm
Tightening torque	8 Nm	Torque for connecting adapter, max.	8.5 Nm
Torque for cap nut, min.	18 Nm	Torque for lock nut, max.	8.5 N/m
Torque for connecting adapter, min.	7.5 Nm	UL 94 flammability rating	V-2
Torque for lock nut, min.	7.5 N/m		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

Approvals

Approvals



ROHS

Conform

Data sheet**VG M50 - K 68**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**

Approval/Certificate/Document of Conformity	EU Declaration of Conformity - Standard plastic cable gland made from Polyamide 6 - DE PS2480 210608 002ISS00
Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	