

ESG 9/11 K MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive |
| Order No. | 1857440000 |
| Type | ESG 9/11 K MC NE WS |
| GTIN (EAN) | 403224840273 1 |
| Qty. | 200 Stück |
| compatible printer | 2715590000 2438520000 2438510000 |

ESG 9/11 K MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.8 mm | Depth (inches) | 0.031 inch |
| Height | 9 mm | Height (inches) | 0.354 inch |
| Width | 11 mm | Width (inches) | 0.433 inch |
| Net weight | 0.45 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

General data

| | | | |
|-----------------------------------|------------------------------|--|---------------|
| Adhesive | Double-sided adhesive tape | Application/manufacturer | Self-adhesive |
| Colour | white | Halogen | No |
| Material | PA 66 | Material colour according to resistance code | 9 |
| Number of markers per combination | 1 MultiCard = Device markers | Operating temperature range | -40...60 °C |
| Operating temperature range, max. | 60 °C | Operating temperature range, min. | -40 °C |
| UL 94 flammability rating | V-2 | Version | Self-adhesive |
| Width | 11 mm | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | EPLAN |
| Product Change Notification | Technical change to MultiCard material - DE Technical change to MultiCard material - EN |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

ESG 9/11 K MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

