

**BZT ZTL6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The transparent cover hood system protects and seals the entire assembly. It is available either as a full-length profile or as an individual cover. It can only be fixed when all connection components are in their initial position. The assembly is optimally protected against unauthorised access without impairing visual inspection.

**General ordering data**

Version	Z-series, Marker holder
Order No.	<a href="#">1781140000</a>
Type	BZT ZTL6
GTIN (EAN)	4032248170364
Qty.	20 pc(s).

**BZT ZTL6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	8.9 mm	Depth (inches)	0.35 inch
Height	9.5 mm	Height (inches)	0.374 inch
Width	7.8 mm	Width (inches)	0.307 inch
Net weight	0.35 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Operating temperature	-40 °C...100 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	100 °C
Continuous operating temp., min.	-40	Continuous operating temp., max.	100

**Material data**

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged		

**Dimensions**

Pitch in mm (P)	5 mm
-----------------	------

**General**

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C		

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">CAT 1 TERM 16/17 EN</a>