

**KLBU 3-8 SC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The shield clamping saddles for direct mounting can be easily and conveniently attached directly to the mounting plate. The products differ in the range of the cable diameter and the thread for fastening the shield clamping saddles.

**General ordering data**

|            |                                     |
|------------|-------------------------------------|
| Version    | Clamping yoke, Clamping yoke, Steel |
| Order No.  | <a href="#">1791220000</a>          |
| Type       | KLBU 3-8 SC                         |
| GTIN (EAN) | 4032248222179                       |
| Qty.       | 100 Stück                           |

## KLBUE 3-8 SC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|                            |         |                 |            |
|----------------------------|---------|-----------------|------------|
| Depth                      | 26 mm   | Depth (inches)  | 1.024 inch |
| Height                     | 18.5 mm | Height (inches) | 0.728 inch |
| Width                      | 14.5 mm | Width (inches)  | 0.571 inch |
| Mounting dimension - width | 13.5 mm | Net weight      | 11.78 g    |

### Temperatures

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

### Material data

|          |       |        |        |
|----------|-------|--------|--------|
| Material | Steel | Colour | silver |
|----------|-------|--------|--------|

### System specifications

|         |                         |
|---------|-------------------------|
| Version | For a shield connection |
|---------|-------------------------|

### Additional technical data

|                          |       |                     |                 |
|--------------------------|-------|---------------------|-----------------|
| Explosion-tested version | No    | Installation advice | Direct mounting |
| Type of mounting         | Screw |                     |                 |

### Conductors for clamping (rated connection)

|                      |      |                      |      |
|----------------------|------|----------------------|------|
| Cable diameter, max. | 8 mm | Cable diameter, min. | 3 mm |
|----------------------|------|----------------------|------|

### General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002020    | ETIM 7.0    | EC002020    |
| ETIM 8.0    | EC002020    | ECLASS 9.0  | 27-14-11-50 |
| ECLASS 9.1  | 27-14-11-50 | ECLASS 10.0 | 27-14-11-50 |
| ECLASS 11.0 | 27-14-11-50 | ECLASS 12.0 | 27-14-11-50 |

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">EAC certificate</a>  |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Engineering Data                            | <a href="#">EPLAN</a>  |
| User Documentation                          | <a href="#">Beipackzettel_KLBUE.pdf</a><br><a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |

Erstellungs-Datum May 30, 2023 3:16:59 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten