

TS 27X12.5M/ST/F.ZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Terminal rails, Rail, DIN EN 60715, Steel
Order No.	1802690000
Type	TS 27X12.5M/ST/F.ZN
GTIN (EAN)	4032248257201
Qty.	2 m

Creation date March 1, 2023 2:21:06 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

TS 27X12.5M/ST/F.ZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	12.5 mm	Depth (inches)	0.492 inch
Height	27 mm	Height (inches)	1.063 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	50 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Mounting rail

Installation advice	Direct mounting		
Length of the terminal rail	min.	0 mm	
	max.	2,000 mm	
	nominal	2,000 mm	
Material	Steel		
Standards	DIN EN 60715		
Surface finish	galvanized		
Thickness	2 mm		

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

TS 27X12.5M/ST/F.ZN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

