

## CLI C 2-18 GE NE SG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 4 - 10 mm, 18 x 6.9 mm, yellow
Order No.	<a href="#">1871831687</a>
Type	CLI C 2-18 GE NE SG
GTIN (EAN)	4032248452217
Qty.	1,000 Stück

Erstellungs-Datum May 22, 2023 12:10:13 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CLI C 2-18 GE NE SG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Height	18 mm	Height (inches)	0.709 inch
Width	6.9 mm	Width (inches)	0.272 inch
Net weight	0.653 g		

### Temperatures

Operating temperature range	-30...60 °C
-----------------------------	-------------

### General data

Colour	yellow	Halogen	Yes
Insulation cross-section, max.	10	Material	PVC, soft, without Cadmium
Material colour according to resistance code	4	Operating temperature range	-30...60 °C
Operating temperature range, max.	60 °C	Operating temperature range, min.	-30 °C
Printing	Neutral	Recommended industries	Process, Machinery
Type of printing	neutral	UL 94 flammability rating	V-0
Version	Loop	Width	6.9 mm

### Conductor and cable markers

Conductor O.D.	4 - 10 mm	Conductor O.D., max.	10 mm
Conductor O.D., min.	4 mm	Conductor cross-section, max.	16 mm <sup>2</sup>
Conductor cross-section, min.	2.5 mm <sup>2</sup>	Cross-section for connected wire	2.5 - 16 mm <sup>2</sup>
Halogen	Yes		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Product Change Notification	<a href="#">PCN CableLine_DE</a> <a href="#">PCN CableLine_EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CLI C 2-18 GE NE SG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**



Similar to illustration