

KSW 4.0 EL WS 50M**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



KSW marking strips are used to identify multi-pole PCB plug-in connectors. Users can print them individually without being confined to a certain pitch.

- Smudge-proof labelling
- Strips 2.5 mm and 4 mm wide
- Simply stick on - finished
- Optimum adhesion
- PVC-free

General ordering data

Version	KSW, Terminal marker, 4 x , Pitch in mm (P): 4.00 Weidmueller, white
Order No.	1812670000
Type	KSW 4.0 EL WS 50M
GTIN (EAN)	4032248296071
Qty.	50 m

KSW 4.0 EL WS 50M

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Height	4 mm	Height (inches)	0.157 inch
Length	50,000 mm	Length (inches)	1,968.5 inch
Net weight	18.3 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate	Application/manufacturer	Weidmueller
Colour	white	Halogen	No
Length	50,000 mm	Material	Polyester, PVC-free
Material colour according to resistance code	9	Number per sheet	20
Operating temperature range	-40...150 °C	Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C	Orientation of print	horizontal and vertical
Printed characters	without	Printing	Neutral
Type of printing	neutral	Version	Self-adhesive

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC000761	ETIM 7.0	EC000761
ETIM 8.0	EC000761	ECLASS 9.0	27-14-11-37
ECLASS 9.1	27-14-11-37	ECLASS 10.0	27-14-11-37
ECLASS 11.0	27-28-11-01	ECLASS 12.0	27-28-11-01

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format

KSW 4.0 EL WS 50M

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings

