

## SAIB-VSA-4P/230/9-H/OB

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Customisable valve plugs are used frequently in special-purpose machine engineering. Such plugs are used to connect solenoid valves. The valve plugs are available in all standard design types. The range includes the design types A, B Industrial, B acc. to DIN, C Industrial and C acc. to DIN. The valve plugs are available in 3 and 4-pole versions without cables. A flat gasket seal is included which, when screwed on, guarantees IP 65 protection.

### General ordering data

Version	Field attachable connector, Valve plug, Socket, angled
Order No.	<a href="#">1873140000</a>
Type	SAIB-VSA-4P/230/9-H/OB
GTIN (EAN)	4032248492510
Qty.	1 pc(s).

## SAIB-VSA-4P/230/9-H/OB

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	29 g	www.weidmueller.com
------------	------	---------------------

## Temperatures

Operating temperature, min.	-25 °C	Operating temperature, max.	85 °C
-----------------------------	--------	-----------------------------	-------

## Technical data customisable plug-in connectors

All valve plugs are fitted with protective circuits	Without circuitry	Cable diameter	6...8 mm (PG9) / 8...10 mm (PG11)
Cable diameter, max.	8 mm	Cable diameter, min.	6 mm
Cable glands	PG 9	Coding	Design A (18 mm)
Conductor cross-section, max.	1.5 mm <sup>2</sup>	Conductor cross-section, min.	0.34 mm <sup>2</sup>
Connection cross-section, max.	1.5 mm <sup>2</sup>	Connection cross-section, min.	0.34 mm <sup>2</sup>
Contact surface	Ni	Housing main material	PA 6 GF
Insulation strength	10 <sup>8</sup> Ω	Number of poles	4
Plugging cycles	≤ 50	Pollution severity	3
Protection degree	IP65	Rated current	10 A
Rated voltage	230 V	Rated voltage	230 V
Temperature range of housing	-25...+85 °C	Type of connection	Screw connection

## Classifications

ETIM 6.0	EC002062	ETIM 7.0	EC003623
ETIM 8.0	EC003623	ECLASS 9.0	27-44-01-05
ECLASS 9.1	27-44-01-05	ECLASS 10.0	27-44-01-05
ECLASS 11.0	27-44-01-05	ECLASS 12.0	27-44-01-05

## Approvals

Approvals



ROHS Conform

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>