

ZP 2.5/2AN/QV/5**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

| | |
|------------|--|
| Version | Z-series, Plug-in connector, dark beige, Direct mounting |
| Order No. | 1815770000 |
| Type | ZP 2.5/2AN/QV/5 |
| GTIN (EAN) | 4032248370405 |
| Qty. | 20 pc(s). |

ZP 2.5/2AN/QV/5

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 41 mm | Depth (inches) | 1.614 inch |
| Height | 37 mm | Height (inches) | 1.457 inch |
| Width | 25 mm | Width (inches) | 0.984 inch |
| Net weight | 27.4 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|-----|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 |
| Continuous operating temp., max. | 120 | | |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-----------------------------------|---|-------------------------------------|----|
| Version | Set of connectors, Cross-connector, pluggable, 2-conductor connection, Tension-clamp connection | End cover plate required | No |
| Number of levels | 1 | Number of clamping points per level | 2 |
| Levels cross-connected internally | No | PE connection | No |

Additional technical data

| | | | |
|---------------------|-----------------|------------|--------|
| Installation advice | Direct mounting | Open sides | closed |
| Type of mounting | Plugged | | |

CSA rating data

| | | | |
|-----------------------------------|----------------|-----------------------------------|--------|
| Certificate number (cCSAus) | 154685-1460993 | Current size C (cCSAus) | 20 A |
| Current size D (cCSAus) | 5 A | Voltage size C (cCSAus) | 300 V |
| Voltage size D (cCSAus) | 600 V | Wire cross section max. (cCSAusX) | 12 AWG |
| Wire cross section min. (cCSAusX) | 26 AWG | | |

Conductors for clamping (rated connection)

| | | | |
|---|----------------------|---|---------------------|
| Blade size | 0.6 x 3.5 mm | Clamping range, max. | 4 mm ² |
| Clamping range, min. | 0.13 mm ² | Connection direction | top |
| Gauge to IEC 60947-1 | A2 | Number of connections | 10 |
| Stripping length | 10 mm | Type of connection | Plug-in connection |
| Wire connection cross section AWG, max. | AWG 26 | Wire connection cross section AWG, min. | AWG 12 |
| Wire connection cross section, finely stranded, max. | 4 mm ² | Wire connection cross section, finely stranded, min. | 0.5 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² |
| Wire connection cross-section, solid core, max. | 4 mm ² | Wire connection cross-section, solid core, min. | 0.5 mm ² |

Creation date March 3, 2023 10:42:09 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

2

ZP 2.5/2AN/QV/5

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Technical data

General

| | | | |
|---|----------------------------------|---|---------------------|
| Installation advice | Direct mounting | Number of poles | www.weidmueller.com |
| Standards | In accordance with IEC 60947-7-1 | Wire connection cross section AWG, max. | AWG 26 |
| Wire connection cross section AWG, min. | AWG 12 | | |

Rating data

| | | | |
|---|----------------------------------|--|---------|
| Rated cross-section | 2.5 mm ² | Rated voltage | 500 V |
| Rated voltage to adjoining terminal | 500 V | Max. voltage of clamp support & pluggable system | 690 V |
| Rated current | 24 A | Current at maximum wires | 24 A |
| Standards | In accordance with IEC 60947-7-1 | Volume resistance according to IEC 60947-7-x | 1.33 mΩ |
| Rated impulse withstand voltage | 6 kV | Rated impulse withstand voltage to adjacent terminal | 6 kV |
| Power loss in accordance with IEC 60947-7-x | 0.77 W | Pollution severity | 3 |

UL rating data

| | | | |
|--|--------|--|--------|
| Certificate No. (cURus) | E60693 | Conductor size Factory wiring max. (cURus) | 12 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Conductor size Field wiring max. (cURus) | 12 AWG |
| Conductor size Field wiring min. (cURus) | 26 AWG | Current size C (cURus) | 20 A |
| Current size D (cURus) | 5 A | Voltage size C (cURus) | 300 V |
| Voltage size D (cURus) | 600 V | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ECLASS 9.0 | 27-14-11-92 |
| ECLASS 9.1 | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E60693 |

Data sheet**ZP 2.5/2AN/QV/5****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.comwww.weidmueller.com**Technical data****Downloads**Approval/Certificate/Document of
Conformity[EAC certificate](#)
[DNVGL certificate](#)
[CB Testreport](#)
[CB Certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures