

**SM 22/22 K MC SDR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	SwitchMark, Device markers, 22 x 22 mm, To customer specification
Order No.	<a href="#">1877580000</a>
Type	SM 22/22 K MC SDR
GTIN (EAN)	4032248467853
Qty.	16 Stück
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

## SM 22/22 K MC SDR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	1 mm	Depth (inches)	0.039 inch
Height	22 mm	Height (inches)	0.866 inch
Width	22 mm	Width (inches)	0.866 inch
Net weight	1.25 g		

### Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

### General data

Adhesive	Double-sided adhesive tape	Colour	To customer specification
Colour of printing	black	Halogen	No
Material	Polyamide 66	Number of markers per combination	1 MultiCard = Device markers
Operating temperature range	-40...60 °C	Operating temperature range, max.	60 °C
Operating temperature range, min.	-40 °C	Printed characters	Based on customer requirements (Please send M-Print PRO file)
Printing method	MC Laser	UL 94 flammability rating	V-2
Version	Self-adhesive	Width	22 mm

### Device markers

Halogen	No
---------	----

### Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**SM 22/22 K MC SDR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

