

## SAIE-M12B-5-0.5U-M16

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

### General ordering data

Version	Built-in plugs, M12, Female socket, straight, M 16, Number of poles: 5, 0.5 m, Front mounting
Order No.	<a href="#">1836910000</a>
Type	SAIE-M12B-5-0.5U-M16
GTIN (EAN)	4032248344901
Qty.	1 pc(s).

**SAIE-M12B-5-0.5U-M16**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 30 g

**Temperatures**

Operating temperature, min. -30 °C

Operating temperature, max. 90 °C

**Technical data customisable plug-in connectors**

Cable glands	M 16	Coding	A
Contact surface	Gold-plated	Housing main material	Zinc diecast
Number of poles	5	Plugging cycles	≥ 100
Protection degree	IP67, when screwed in	Rated current	4 A
Rated voltage	60 V	Rated voltage	250 V (4-pole) / 125 V (5-pole) / 60 V (8-pole)
Temperature range of housing	-30...+90 °C		

**Standards**

Connector standard IEC 61076-2-101

**General data**

Cable glands	M 16	Cable length	0.5 m
Coding	A	Conductor O.D.	-
Connection thread	M12	Contact surface	Gold-plated
Core cross-section	0.34 mm <sup>2</sup>	Housing main material	Zinc diecast
Material	PVC	Mounting thread	M 16
Number of poles	5	Plugging cycles	≥ 100
Protection degree	IP67, when screwed in	Rated current	4 A
Rated voltage	60 V	Rated voltage	250 V (4-pole) / 125 V (5-pole) / 60 V (8-pole)
Strand / cable length	0.5 m	Temperature range of housing	-30...+90 °C
Type of mounting	Front mounting		

**Classifications**

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ECLASS 9.0	27-44-01-03
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-03
ECLASS 11.0	27-44-01-03	ECLASS 12.0	27-44-01-03

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	4060c755-8d0b-4d43-bdb3-4ffabe9d7497

**SAIE-M12B-5-0.5U-M16****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

**Data sheet****SAIE-M12B-5-0.5U-M16****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Drawings****Wiring diagram****Pole scheme**