

TS 35X15/5X18 2M/ST/ZN**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

Similar to illustration

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Rail, TS 35, TS 35 x 15, with slot, Steel, galvanic zinc plated and passivated
Order No.	1837380000
Type	TS 35X15/5X18 2M/ST/ZN
GTIN (EAN)	4032248346547
Qty.	2 m

TS 35X15/5X18 2M/ST/ZN

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	15 mm	Depth (inches)	0.591 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	620 g		

Mounting rail

Installation advice	Direct mounting		
Length of the terminal rail	min.	0 mm	
	nominal	2,000 mm	
	max.	2,000 mm	
Material	Steel		
Mounting rail not punchable	Yes		
Pre-punched mounting rail	Yes		
Short circuit strength corresponds to E-Cu wire	50 mm ²		
Short-time withstand current according to IEC 60947-7-2	6 kA/1s		
Slit gap	7 mm		
Slit gap			
Slit length	18 mm		
Slit length			
Slit width	5.2 mm		
Slit width			
Standards	In accordance with DIN EN 60715		
Surface finish	galvanic zinc plated and passivated		

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

TS 35X15/5X18 2M/ST/ZN**Weidmüller Interfaces GmbH & Co. KG**



Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Drawings**Product image**

Similar to illustration