

**ZT 4/4AN/2****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Some applications demand for a pluggable, modular solution to be more flexible or to facilitate the installation. Where complete functional units have to be prefabricated or replaced, modular and flexible connection systems are required. Our pluggable terminal blocks can be quickly assembled and are completely factory tested.

**General ordering data**

|            |  |
|------------|--|
| Version    | Z-series, Feed-through terminal, Rated cross-section: 4 mm <sup>2</sup> , Plug-in connection, dark beige |
| Order No.  | <a href="#">1848350000</a>   |
| Type       | ZT 4/4AN/2   |
| GTIN (EAN) | 4032248403516  |
| Qty.       | 50 pc(s).  |

## ZT 4/4AN/2

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                |            |
|--------------------------|------------|----------------|------------|
| Depth                    | 43 mm      | Depth (inches) | 1.693 inch |
| Depth including DIN rail | 43.5 mm    | Height         | 100.5 mm   |
| Height (inches)          | 3.957 inch | Width          | 6.5 mm     |
| Width (inches)           | 0.256 inch | Net weight     | 18.06 g    |

## Temperatures

|                                  |                |                                  |     |
|----------------------------------|----------------|----------------------------------|-----|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 |
| Continuous operating temp., max. | 120            |                                  |     |

## Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

## System specifications

|                               |  |                                     |       |
|-------------------------------|--|-------------------------------------|-------|
| Version                       | 2 tension-clamp connections - 2 plug-in connections, pluggable | End cover plate required            | Yes   |
| Number of levels              | 1  | Number of clamping points per level | 2     |
| Number of potentials per tier | 1  | Levels cross-connected internally   | No    |
| PE connection                 | No   | Rail                                | TS 35 |

## Additional technical data

|                          |         |            |       |
|--------------------------|---------|------------|-------|
| Explosion-tested version | No      | Open sides | right |
| Type of mounting         | Snap-on |            |       |

## CSA rating data

|                               |                |                               |        |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-1720292 | Current size C (CSA)          | 28 A   |
| Voltage size C (CSA)          | 600 V          | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG         |                               |        |

## Conductors for clamping (additional connection)

|   |                   |  |                    |
|---|-------------------|--|--------------------|
| Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max. | 4 mm <sup>2</sup> | Connection type, additional connection | Plug-in connection |
|---|-------------------|--|--------------------|

## Conductors for clamping (rated connection)

|                       |                      |
|-----------------------|----------------------|
| Blade size            | 0.6 x 3.5 mm         |
| Clamping range, max.  | 6 mm <sup>2</sup>    |
| Clamping range, min.  | 0.13 mm <sup>2</sup> |
| Connection direction  | top                  |
| Gauge to IEC 60947-1  | A3                   |
| Number of connections | 2                    |
| Stripping length      | 12 mm                |

## ZT 4/4AN/2

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

## Technical data

Fax. +49 5231 14-2083

|   |   |  |                      |                      |
|---|---|--|----------------------|----------------------|
| Tube length for twin wire-end ferrule   | Cross-section for conductor connection                              | nominal                                | 0.5 mm <sup>2</sup>  |                      |
|   |   | min.                                   | 8 mm                 |                      |
|   |   | max.                                   | 12 mm                |                      |
|   | Cross-section for conductor connection                              | nominal                                | 0.75 mm <sup>2</sup> |                      |
|   |   | min.                                   | 8 mm                 |                      |
|   |   | max.                                   | 12 mm                |                      |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4                        | Cross-section for conductor connection                              | nominal                                | 0.5 mm <sup>2</sup>  |                      |
|   |   | min.                                   | 8 mm                 |                      |
|   |   | max.                                   | 10 mm                |                      |
|   | Cross-section for conductor connection                              | nominal                                | 0.75 mm <sup>2</sup> |                      |
|   |   | min.                                   | 6 mm                 |                      |
|   |   | max.                                   | 12 mm                |                      |
|   | Cross-section for conductor connection                              | nominal                                | 1 mm <sup>2</sup>    |                      |
|   |   | min.                                   | 6 mm                 |                      |
|   |   | max.                                   | 12 mm                |                      |
|   | Cross-section for conductor connection                              | nominal                                | 1.5 mm <sup>2</sup>  |                      |
|   |   | min.                                   | 8 mm                 |                      |
|   |   | max.                                   | 12 mm                |                      |
|   | Cross-section for conductor connection                              | nominal                                | 2.5 mm <sup>2</sup>  |                      |
|   |   | min.                                   | 8 mm                 |                      |
|   |   | max.                                   | 12 mm                |                      |
|   | Cross-section for conductor connection                              | nominal                                | 4 mm <sup>2</sup>    |                      |
|   |   | min.                                   | 10 mm                |                      |
|   |   | max.                                   | 12 mm                |                      |
|   | Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Cross-section for conductor connection | nominal              | 0.5 mm <sup>2</sup>  |
|   |   |  | nominal              | 10 mm                |
|   |   | Cross-section for conductor connection | nominal              | 0.75 mm <sup>2</sup> |
|   |   |  | nominal              | 10 mm                |
|   |   | Cross-section for conductor connection | nominal              | 1 mm <sup>2</sup>    |
|   |   |  | nominal              | 10 mm                |
| Cross-section for conductor connection  |   | nominal                                | 1.5 mm <sup>2</sup>  |                      |
|   |   | min.                                   | 10 mm                |                      |
|   |   | max.                                   | 12 mm                |                      |
| Cross-section for conductor connection  |   | nominal                                | 2.5 mm <sup>2</sup>  |                      |
|   |   | min.                                   | 10 mm                |                      |
|   |   | max.                                   | 12 mm                |                      |
| Cross-section for conductor connection  |   | nominal                                | 4 mm <sup>2</sup>    |                      |
|   |   | nominal                                | 12 mm                |                      |
| Type of connection  |   | Plug-in connection                     |                      |                      |
| Wire connection cross section AWG, max.   |   | AWG 10                                 |                      |                      |
| Wire connection cross section AWG, min.   |   | AWG 26                                 |                      |                      |
| Wire connection cross section, finely stranded, max.                                    |   | 6 mm <sup>2</sup>                      |                      |                      |
| Wire connection cross section, finely stranded, min.                                    |   | 0.5 mm <sup>2</sup>                    |                      |                      |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. |   | 4 mm <sup>2</sup>                      |                      |                      |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. |   | 0.5 mm <sup>2</sup>                    |                      |                      |
| Wire connection cross-section, solid core, max.   |   | 6 mm <sup>2</sup>                      |                      |                      |
| Wire connection cross-section, solid core, min.   |   | 0.5 mm <sup>2</sup>                    |                      |                      |

## ZT 4/4AN/2

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

## Technical data

## General

|   |        |   |  |
|---|--------|---|--|
| Rail                                    | TS 35  | Standards                               | www.weidmueller.com In accordance with IEC 60947-7-1 |
| Wire connection cross section AWG, max. | AWG 10 | Wire connection cross section AWG, min. | AWG 26   |

## Rating data

|  |                   |                                 |                                  |
|--|-------------------|---------------------------------|----------------------------------|
| Rated cross-section                              | 4 mm <sup>2</sup> | Rated voltage                   | 800 V                            |
| Max. voltage of clamp support & pluggable system | 800 V             | Rated current                   | 32 A                             |
| Current at maximum wires                         | 32 A              | Standards                       | In accordance with IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x     | 1 mΩ              | Rated impulse withstand voltage | 8 kV                             |
| Power loss in accordance with IEC 60947-7-x      | 1.02 W            | Pollution severity              | 3                                |

## UL rating data

|  |        |  |        |
|--|--------|--|--------|
| Certificate No. (cURus)                    | E60693 | Conductor size Factory wiring max. (cURus) | 10 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Conductor size Field wiring max. (cURus)   | 10 AWG |
| Conductor size Field wiring min. (cURus)   | 26 AWG | Current size C (cURus)                     | 28 A   |
| Voltage size C (cURus)                     | 600 V  |  |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
| ETIM 8.0    | EC000897    | ECLASS 9.0  | 27-14-11-20 |
| ECLASS 9.1  | 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| ECLASS 11.0 | 27-14-11-20 | ECLASS 12.0 | 27-14-11-20 |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E60693     |

## Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">EAC certificate</a><br><a href="#">Declaration of Conformity</a><br><a href="#">CE Declaration of Conformity all terminals</a><br><a href="#">UKCA declaration of conformity</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Engineering Data                            | <a href="#">WSCAD, Zuken E3.S</a>  |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>  |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                                   |  |

Creation date February 28, 2023 1:08:00 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**Data sheet**

**ZT 4/4AN/2**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

