

## CC 15/27 MC NE SI

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration

ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	ClipCard, Device markers, 15 x 27 mm, Holder CC-H 15/27, silver
Order No.	<a href="#">1876760000</a>
Type	CC 15/27 MC NE SI
GTIN (EAN)	4032248467266
Qty.	80 Stück
Alternative product	<a href="#">1079550000</a>
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

Erstellungs-Datum May 22, 2023 12:22:03 PM CEST

## CC 15/27 MC NE SI

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	1 mm	Depth (inches)	0.039 inch
Height	15 mm	Height (inches)	0.591 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	1.363 g		

### Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

### General data

Application/manufacture	Holder CC-H 15/27	Colour	silver
Halogen	No	Material	Polyamide 66
Material colour according to resistance code	4	Number of markers per combination	1 MultiCard = Device markers
Operating temperature range	-40...100 °C	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Recommended industries	Machinery
UL 94 flammability rating	V-2	Width	27 mm

### Device markers

Halogen	No
---------	----

### Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Datenblatt**

**CC 15/27 MC NE SI**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

