

ESG 6/15 K MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ESG, Device markers x 15 mm, PA 66, Colour: To customer specification, Self-adhesive
Order No.	1880090000
Type	ESG 6/15 K MC SDR
GTIN (EAN)	4032248478774
Qty.	40 Stück
compatible printer	2715590000 2438520000 2438510000

ESG 6/15 K MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	1 mm	Depth (inches)	0.039 inch
Height	6 mm	Height (inches)	0.236 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	0.325 g		

Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

General data

Adhesive	Double-sided adhesive tape	Application/manufacturer	Self-adhesive
Colour	To customer specification	Colour of printing	black
Halogen	No	Material	PA 66
Number of markers per combination	1 MultiCard = Device markers	Operating temperature range	-40...60 °C
Operating temperature range, max.	60 °C	Operating temperature range, min.	-40 °C
Printed characters	Based on customer requirements (Please send M-Print PRO file)	Printing method	MC Laser
UL 94 flammability rating	V-2	Version	Self-adhesive
Width	15 mm		

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

ESG 6/15 K MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

