

## VG PG11-K67

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

### Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, PG 11, 8 mm, OD min. 5 - OD max. 10 mm, Polyamide 6
Order No.	<a href="#">1909780000</a>
Type	VG PG11-K67
GTIN (EAN)	4032248536702
Qty.	50 pc(s).

## VG PG11-K67

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	37 mm	Length (inches)	1.457 inch
Net weight	8.78 g		

## Temperatures

Operating temperature	-20 °C...80 °C	Operating temperature, min.	-20 °C
Operating temperature, max.	80 °C		

## General information

AF size 1	22 mm	Cable glands	PG
External thread	PG 11	Halogen	No, Yes
Length of thread	8 mm	Material	Polyamide 6
Operating temperature range, max.	100 °C	Operating temperature range, min.	-20 °C
Outer cable diameter, max.	10 mm	Outer cable diameter, min.	5 mm
Pitch of thread	1.41 mm	Protection degree	IP67
Seal insert	NBR	Silicone	No
Tightening torque	2 Nm	Torque for cap nut, max.	3 Nm
Torque for cap nut, min.	2 Nm	Torque for connecting adapter, max.	2.5 Nm
Torque for connecting adapter, min.	1.5 Nm	Torque for lock nut, max.	2.5 N/m
Torque for lock nut, min.	1.5 N/m	UL 94 flammability rating	V-2

## Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

## Approvals

Approvals



ROHS

Conform

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	