

CLI C 3-33 SDR SG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 8 - 16 mm, 33 x 11 mm, To customer specification
Order No.	1912800000
Type	CLI C 3-33 SDR SG
GTIN (EAN)	4032248542642
Qty.	100 Stück

Erstellungs-Datum May 22, 2023 12:50:41 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CLI C 3-33 SDR SG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	17 mm	Depth (inches)	0.669 inch
Height	33 mm	Height (inches)	1.299 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	4.125 g		

Temperatures

Operating temperature range	80 °C
-----------------------------	-------

General data

Colour	To customer specification	Colour of printing	black
Halogen	Yes	Material	PVC, soft, without Cadmium
Operating temperature range	80 °C	Operating temperature range, max.	80 °C
Orientation of print	horizontal	Printed characters	To customer specification
Printing	Custom printing	Printing method	Ink jet technology
Type of printing	To customer specification	UL 94 flammability rating	V-0
Version	Loop	Width	11 mm

Conductor and cable markers

Conductor O.D.	8 - 16 mm	Conductor O.D., max.	16 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	70 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 70 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Product Change Notification	PCN CableLine_DE PCN CableLine_EN
Catalogues	Catalogues in PDF-format

CLI C 3-33 SDR SG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen



Similar to illustration