

SF 00/12 MC SDR V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format



General ordering data

| | |
|--------------------|--|
| Version | SlimFix, Conductor and cable markers, 1 - 1.3 mm, 12 x 3.2 mm, To customer specification |
| Order No. | 1919300000 |
| Type | SF 00/12 MC SDR V2 |
| GTIN (EAN) | 4032248555697 |
| Qty. | 80 Stück |
| compatible printer | 2715590000 2438520000 2438510000 |

SF 00/12 MC SDR V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 3.2 mm | Depth (inches) | 0.126 inch |
| Height | 12 mm | Height (inches) | 0.472 inch |
| Width | 3.2 mm | Width (inches) | 0.126 inch |
| Net weight | 0.258 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|--|-----------------------------------|---|
| Advice label | Colour based on customer requirements (Please send M-Print PRO file) | Colour | To customer specification |
| Colour of printing | black | Halogen | No |
| Material | Polyamide 66 | Number of markers per combination | 1 MultiCard = Conductor and cable markers |
| Operating temperature range | -40...100 °C | Operating temperature range, max. | 100 °C |
| Operating temperature range, min. | -40 °C | Orientation of print | horizontal |
| Printed characters | Based on customer requirements (Please send M-Print PRO file) | Printing method | MC Laser |
| Size of labelling field | 12 x 3.2 mm | Type of printing | To customer specification |
| UL 94 flammability rating | V-2 | Width | 3.2 mm |

Conductor and cable markers

| | | | |
|-------------------------------|----------------------|----------------------------------|-----------------------------|
| Conductor O.D. | 1 - 1.3 mm | Conductor O.D., max. | 1.3 mm |
| Conductor O.D., min. | 1 mm | Conductor cross-section, max. | 0.25 mm ² |
| Conductor cross-section, min. | 0.25 mm ² | Cross-section for connected wire | 0.25 - 0.25 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |