

HDC 10A SLU 1M25G

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Size: 2, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, Size of cable entries: M 25
Order No.	1901160000
Type	HDC 10A SLU 1M25G
GTIN (EAN)	4032248586189
Qty.	1 pc(s).

HDC 10A SLU 1M25G

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Height	57 mm	Height (inches)	2.244 inch
Width	62.7 mm	Width (inches)	2.468 inch
Mounting dimension - height	40 mm	Mounting dimension - width	48 mm
Net weight	199 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Dimensions

Cable entry	w. thread	Height of base B1	4 mm
Height of housing B	57 mm	Hole pitch length A2	48 mm
Total length housing	63 mm	Width base C1	50 mm
Width housing C	29.5 mm		

General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating	Tightening torque	0.5 Nm

Version

BG	2	Cable entry	w. thread
Clamp version	End-locking clamp	Colour (RAL)	RAL 7035
Design	Standard	Design of housing	Base housing
Design of locking system	End-locking clamp, lower side	Internal thread	M 25
Number of cable entry on top	0	Number of cable entry sideways	1
Size	2	Size of cable entries	M 25
Suitable for ModuPlug®	No	Tightening torque	0.5 Nm
Top part/bottom part/lid	lower part	Type	Base housing

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant
Substance	Ethyl alcohol
Chemical resistance	Resistant
Substance	Transmission oil

Creation date March 6, 2023 1:09:42 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

HDC 10A SLU 1M25G

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Chemical resistance	Resistant
Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	e98b2b24-ba23-41bf-8d19-0dda3647412f
Chemical resistance	de.myview.objectmodel.impl.BlockImpl@36458352 de.myview.objectmodel.impl.BlockImpl@4d081bb4 de.myview.objectmodel.impl.BlockImpl@3e3cbe49 de.myview.objectmodel.impl.BlockImpl@37aa6d4a de.myview.objectmodel.impl.BlockImpl@2d6f27fe de.myview.objectmodel.impl.BlockImpl@20375c5c de.myview.objectmodel.impl.BlockImpl@7ba260e5 de.myview.objectmodel.impl.BlockImpl@1f0692e6 de.myview.objectmodel.impl.BlockImpl@4b82162f de.myview.objectmodel.impl.BlockImpl@51cd66bf de.myview.objectmodel.impl.BlockImpl@3900812b de.myview.objectmodel.impl.BlockImpl@12bab54f de.myview.objectmodel.impl.BlockImpl@4952ea59

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Product Change Notification	20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

Creation date March 6, 2023 1:09:42 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.