

VG H M40 MS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG H (HDC halved cable gland), Cable glands, straight, M 40, 9.5 mm, OD min. 23 - OD max. 32 mm, IP65, Brass, nickel-plated
Order No.	1921770000
Type	VG H M40 MS
GTIN (EAN)	4032248563036
Qty.	10 pc(s).

Creation date March 9, 2023 12:58:00 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

VG H M40 MS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	40 mm	Width (inches)	1.575 inch
Net weight	45.3 g		

Temperatures

Operating temperature	-20 °C...60 °C	Operating temperature, min.	-20 °C
Operating temperature, max.	60 °C		

General information

AF size	40 mm	AF size 1	40 mm
Cable glands	metric, M 40	External thread	M 40
Halogen	Yes	Length of thread	9.5 mm
Material	Brass, nickel-plated	Notch multi-layer sealing diameter 1	23 mm
Notch multi-layer sealing diameter 2	26 mm	Notch multi-layer sealing diameter 3	29 mm
Notch multi-layer sealing diameter 4	32 mm	O-Ring	NBR
Operating temperature range, max.	60 °C	Operating temperature range, min.	-20 °C
Outer cable diameter, max.	32 mm	Outer cable diameter, min.	23 mm
Pitch of thread	1.5 mm	Protection degree	IP65
Protection degree with GWDR	IP65	Sealing	NBR

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	