

VT SF 5/12 MC SDR V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format



General ordering data

Version	SlimFix, Conductor and cable markers, 4.7 - 7.4 mm, 12 x 7.4 mm, To customer specification
Order No.	1906320000
Type	VT SF 5/12 MC SDR V0
GTIN (EAN)	4032248528738
Qty.	32 Stück
Alternative product	1919660000
compatible printer	2715590000 2438520000 2438510000

VT SF 5/12 MC SDR V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Height	12 mm	Height (inches)	0.472 inch
Width	7.4 mm	Width (inches)	0.291 inch
Net weight	0.5 g		

Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

General data

Advice label	Colour based on customer requirements (Please send M-Print PRO file)	Colour	To customer specification
Colour of printing	black	Halogen	No
Material	Polyamide 66	Number of markers per combination	1 MultiCard = Conductor and cable markers
Operating temperature range	-50...120 °C	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Orientation of print	horizontal
Printed characters	Based on customer requirements (Please send M-Print PRO file)	Printing method	MC Laser
Size of labelling field	12 x 7.4 mm	Type of printing	To customer specification
UL 94 flammability rating	V-0	Width	7.4 mm

Conductor and cable markers

Conductor O.D.	4.7 - 7.4 mm	Conductor O.D., max.	7.4 mm
Conductor O.D., min.	4.7 mm	Conductor cross-section, max.	10 mm ²
Conductor cross-section, min.	6 mm ²	Cross-section for connected wire	6 - 10 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format