

## SAIL-M12WM12W-3-3.0V

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

### General ordering data

|            |  |
|------------|--|
| Version    | Sensor/actuator line, Connecting line, M12 / M12, Number of poles : 3, 3 m, pin, 90&deg; - socket 90&deg;; Shielded: No, LED: No, Sheath material: PVC, Halogen: Yes |
| Order No.  | <a href="#">1925380300</a>   |
| Type       | SAIL-M12WM12W-3-3.0V   |
| GTIN (EAN) | 4032248569663  |
| Qty.       | 1 pc(s).   |

Creation date March 16, 2023 6:33:54 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## SAIL-M12WM12W-3-3.0V

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 130 g

### Temperatures

Operating temperature, min. -25 °C Operating temperature, max. 80 °C

### Technical specifications for cable

|  |                      |                           |                      |
|--|----------------------|---------------------------|----------------------|
| Cable length                                   | 3 m                  | Colour coding             | brown, blue, black   |
| Configurable cable length                      | Yes                  | Core cross-section        | 0.34 mm <sup>2</sup> |
| Halogen  | Yes                  | Insulation                | PVC                  |
| Irradiation crosslinked                        | No                   | Number of poles           | 3                    |
| Outer cladding in accordance with UL AWM style | 2464 (80 °C / 300 V) | Outside diameter          | 4.9 mm ± 0.2 mm      |
| Resistant to welding beads                     | No                   | Sheath material           | PVC                  |
| Sheathing colour                               | black                | Shielded                  | No                   |
| Suitable for cable carriers                    | No                   | Temperature range, moving | -5...80 °C           |
| Temperature range, stationary                  | -30...80 °C          | Torsion resistance        | 0 °/m                |
| Welding spark resistance                       | No                   |                           |                      |

### General technical data

|                              |  |  |                         |
|------------------------------|--|--|-------------------------|
| Coding                       | A  | Connection thread                      | M12 / M12               |
| Contact surface              | Gold-plated                                | Housing main material                  | PUR                     |
| Insulation strength          | 10 <sup>8</sup> Ω                          | LED                                    | No                      |
| Plugging cycles              | ≥ 100                                      | Pollution severity                     | 3                       |
| Protection degree            | IP67, IP68, when fully mounted, IP65, IP66 | Rated current                          | 4 A                     |
| Rated voltage                | 250 V                                      | Shock and vibration proof according to | Section B               |
| Temperature range of housing | -40 ... +85 °C                             | Threaded ring material                 | Diecast zinc            |
| Tightening torque            | M12: 0.8 - 1.2 Nm                          | Version                                | pin, 90°; - socket 90°; |
| jumpered                     | No   |  |                         |

### Electrical properties

Insulation strength 10<sup>8</sup> Ω Rated voltage 250 V

### General standards

Certificate no. (cULus) E307231 Connector standard IEC 61076-2-101

### Standards

Connector standard IEC 61076-2-101 Shock and vibration proof according to Section B

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001855    | ETIM 7.0    | EC001855    |
| ETIM 8.0    | EC001855    | ECLASS 9.0  | 27-06-03-11 |
| ECLASS 9.1  | 27-06-03-11 | ECLASS 10.0 | 27-06-03-11 |
| ECLASS 11.0 | 27-06-03-11 | ECLASS 12.0 | 27-06-03-11 |

**SAIL-M12WM12W-3-3.0V**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Environmental Product Compliance**

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 1c533b66-fcff-4da5-b89f-fd55fbf5cb55 |

**Approvals**

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E307231    |

**Downloads**

|                             |   |
|-----------------------------|---|
| Engineering Data            | <a href="#">WSCAD</a>   |
| Product Change Notification | <a href="#">DE - Technische Änderung zu M12 Gewinding mit 6-Kant</a><br><a href="#">EN - Technical change to M12 nut with additional hexagonal mounting</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>  |
| Brochures                   | <a href="#">FL FIELDWIRING EN</a><br><a href="#">FL FIELDWIRING EN</a>  |

**SAIL-M12WM12W-3-3.0V**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Drawings**

**Dimensioned drawing**




Male, angled

**Pole scheme**




4  
Male

**Dimensioned drawing**



Angled socket

**Pole scheme**



4  
Socket

**Wiring diagram**



**The ideal tool: Screwty® with torque function**



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F